



Specifications:

- Body material: Polythylene
- Voltage rating: 380Vac (RMS)
- Max. temperature: 60°C

Current rating	Dimensions (mm)						
	Cable entry diameter	A	B	C	D	E	F
3A	2.85	8.00	8.00	16.00	13.60	16.00	93.00