Kwik Snap Terminal blocks

A range of VDE approved 12 pole terminal blocks in 24A, 32A, 57A and 76A options. All products are manufactured from white UL94-V2 grade Polypropylene, have a formed zinc plated steel insert and feature 'Kwik-Snap' pole removal without tools. However, although the blocks can easily be divided into the required number of terminals, the pole dividers are still strong enough to support screws for terminal block assembly.

Features & Benefits:

- ✓ Easy, Kwik & clean break No tools required
- ✓ Pole dividers support screws for assembly
- ✓ VDE approved & rated to T85-110
- ✓ Formed, zinc plated steel insert



Specification:-

Ambient Termperature: T85-T110 C

All products comply with IEC/EN60998-1,60998-2-1

Hylec-APL Part Number	Volts (V)	Amps (A) VDE / IEC- rated	Max Wiring Capacity (Sq. mm)	Height	Width	Length	Pitch
HYKS-02412PP	450	24	4	12.2	93.5	17.8	8
HYKS-03212PP	450	32	6	14	116.5	20	10
HYKS-05712PP	450	57	10	16.3	139.3	23.4	12
HYKS-07612PP	750	76	16	20.9	169.5	27.7	14.5

