



4K 2-Port HDMI Splitter

4K@30Hz, AC Powered, Black

Part No.: [207669](#)

EAN-13: 0766623207669 | UPC: 766623207669

Easily distribute a single Ultra-High-Definition (UHD) signal to multiple displays

The Manhattan 4K 2-Port HDMI Splitter with built-in booster streams a 4K HDMI signal from a single UHD source to up to two UHD displays.

Flexible Solution for Many A/V Applications

Ideal for trade shows, classrooms, video conferencing, home theater, presentations and retail applications, the Manhattan 4K HDMI Splitter features a built-in booster for added signal strength. It's a good choice for splitting and distributing a synchronous signal to multiple 4K HDMI displays when source equipment is remotely stored in a secured room or cabinet. Cascade multiple units up to three levels to output HDMI video/audio on additional displays in widely distributed applications.

Quality Construction and Easy Installation

Full compliance with HDMI, HDCP 1.4 and DVI 1.0 ensures that the Manhattan HDMI Splitter can provide long service and reliable performance. Quickly connect HDMI cables (not included) and the AC power adapter, and this affordable UHD solution is complete — no software/hardware configuration or complicated settings required.

Features:

- Duplicates an Ultra-High-Definition (UHD) digital audio/video signal for

For more information on Manhattan products, consult your local dealer or visit www.manhattan-products.com.

All names of products or services mentioned herein are trademarks or registered trademarks of their respective owners. Distribution and reproduction of this document, and use and disclosure of the contents herein, are prohibited unless specifically authorized.

up to two UHD HDMI displays

- 4K@30Hz resolution, full 3D video and Deep Color
- Supports video amplifier bandwidth up to 340 MHz, 3.4 Gbps per channel (10.2 Gbps total) for 4Kx2K displays
- Supports compressed DTS-HD Master Audio and 7.1 surround sound as well as Dolby TrueHD and uncompressed LPCM 8 channel audio
- Supports 48-bit Deep Color (12-bits per channel) and xvYCC (x.vColor)
- Supports LPCM, DTS Digital, DTS-HD Master Audio and Dolby TrueHD audio
- HDCP compliant
- AC powered with Plug and Play installation; no special setup or remote required
- Up to three splitters may be cascaded to support four 4K displays
- Gold-plated contacts for corrosion-free connections
- Works with Playstation and Xbox game systems, Blu-ray players, set-top boxes, satellite receivers and more
- Three-year warranty

Specifications:

Standards and Certifications

- HDCP 1.4
- DVI 1.0
- CTS 1.4a
- CE
- FCC
- RoHS

General

- Source-to-splitter range: up to 15 m (49 ft.)
- Splitter-to-display range: up to 15 m (49 ft.)
- Power: 5 VDC; AC power adapter, 0.9 m (2.9 ft.)

Connections

- One HDMI port (female), 19-pin (input)
- Two HDMI ports (female), 19-pin (output)
- One DC power female, OD 3.5 mm / ID 1.3 mm (input)

Signal Input/Output

- Input video signal: 0.5 – 1.0 V p-p
- Input DDC signal: 5 V p-p (TTL)
- Maximum single-link range: 3840x2160 at 30 Hz, 4096x2160 at 24 Hz resolution
- Output video: HDCP 1.4, DVI 1.0, supports 3D
- Frequency: 3.4 Gbps / 340 MHz

Video Resolutions

For more information on Manhattan products, consult your local dealer or visit www.manhattan-products.com.

All names of products or services mentioned herein are trademarks or registered trademarks of their respective owners. Distribution and reproduction of this document, and use and disclosure of the contents herein, are prohibited unless specifically authorized.

- DTV/HDTV: 480i/480p/576i/576p/720p/1080i/1080p/4K@30Hz

Physical

- LED indicators: power and port connection
- Dimensions: 75 x 49 x 16 mm (3 x 1.9 x 0.6 in.)
- Power adapter: 5 VDC / 1 A; 0.9 m (2.9 ft.)
- Weight: 42 g (0.09 lb.)
- Housing: plastic

Operating Environment

- Operation Temperature: 0 – 40°C (32 – 104°F)
- Storage Temperature: -20 – 60°C (-4 – 140°F)
- Humidity (noncondensing): 0 – 96%

Package Contents

- 4K 2-Port HDMI Splitter
- AC power adapter
- Quick Instruction Guide



