



## **Power Extension Cable C13 to C14, 1 m**

**Power Cord with C13 Female to C14 Male, 10 A, 250 V, Connects a PDU or UPS to a Server, Switch, Storage System and More, Black**

Part No.: [352673](#)

EAN-13: 0766623352673 | UPC: 766623352673

---

### **C13 to C14 PDU Power Cable 1m - Extension Cord for Reliable Power Distribution in Rack-Mount Applications and IT environments**

The Power Extension Cable (C13 Female to C14 Male, 10 A, 250 V) from Intellinet Network Solutions is designed to deliver dependable power in IT and networking environments. Whether you're working in a data center, server room, or enterprise rack setup, this cable provides a simple, effective way to connect servers, switches, storage systems, monitors, or printers to a PDU, UPS, or another compatible power source.

#### **Extended Reach and Flexibility**

Ideal for rack mount applications, this extension cable helps you reach distant power connections or reposition devices more effectively within tight enclosures. It also serves as a practical solution for extending an existing C13 power cord, allowing you to improve cable routing and maintain a tidy installation.

#### **Features:**

- Connects devices like server, computer, monitor and printer to a PDU,

For more information on Manhattan products, consult your local dealer or visit [www.manhattan-products.com](http://www.manhattan-products.com).

All names of products or services mentioned herein are trademarks or registered trademarks of their respective owners. Distribution and reproduction of this document, and use and disclosure of the contents herein, are prohibited unless specifically authorized.

UPS or other power supply, great for rackmount network applications

- Extends a C13 to AC power cable for an enhanced reach to a wall outlet
- Pure bare copper wire for maximum conductivity
- Flexible, durable PVC jacket with heavy-duty strain relief
- High-temperature resistance for use in areas that are not air conditioned
- Great for use with Intellinet 19" Rackmount Smart PDU (#163682)
- For indoor use only
- Lifetime warranty

## **Specifications:**

### Standards and Certifications

- CE
- RoHS
- REACH
- IEC 60320
- VDE
- UKCA

### General

- One IEC 60320 C14 male
- One IEC 60320 C13 female
- Maximum current: 10.0 A
- Maximum voltage: 250.0 V AC

### Physical

- Wire: 100% pure bare copper (Cu)
- Jacket and boot material: PVC
- Number of cores: 3
- Number of strands / strand thickness: 32 / 0.2 mm
- Insulation thickness: 0.6 mm
- Jacket thickness: 0.8 mm
- Nominal overall diameter: 6.8 mm
- Length: 1 m
- Cable type: H05VV-F 3G 1.0 mm<sup>2</sup>
- Net weight: 105 g
- Gross weight: 110 g

### Environmental

- Operation temperature: -10 to 60°C
- Operating humidity (non-condensing): 10 to 85%
- Storage temperature: -20 to 70°C
- Storage humidity (non-condensing): 5 to 90%

### Package Contents

- Power Extension Cord C13 to C14, 1m

