

NS-M1500BLACK

NEOMOUNTS FLOOR STAND

SPECIFICATIONS

GENERAL

Min. screen size*	32 inch
Max. screen size*	65 inch
Min. weight	0 kg (per screen)
Max. weight	50 kg (per screen)
Screens	1
VESA minimum	200x200 mm
VESA maximum	600x400 mm

FUNCTIONALITY

Type	Tilt
Height adjustment	110-143,5 cm
Tilt (degrees)	15°
Adjustment type	Manual

INFORMATION

Color	Black
Main material	Steel
Warranty	5 year
EAN code	8717371448080

*Please note: The inch sizes stated are just an indication, combined with the weight and VESA sizes. The maximum weight and VESA size are absolute restrictions for the products and should not be exceeded.



Neomounts



Neomounts

Neomounts Mobile Monitor/TV Floor Stand for 32-65" screen - Black

The Neomounts floor stand, model NS-M1500BLACK is a mobile floor stand for flat screens up to 65" (165 cm). This mobile stand is a great choice for space saving placement or when wall-, ceiling mounting or desk placement is not an option. This cart stretches your investment by serving a variety of projection needs by sharing a large display over multiple rooms. Get optimal positioning for both standing and seated audiences, in any application, in any part of your location.

Neomounts versatile tilt (15°) technology allows the mount to change to multiple viewing angles to fully benefit from the capabilities of the flat screen. The mount is manually height adjustable from 110 to 144 centimetres. An innovative cable management conceals and routes cables from mount to flat screen. Hide your cables to keep the stand nice and tidy.

Neomounts' floor stand, NS-M1500BLACK holds your TV, AV equipment and even hides your cables. The casters allow the stand to move it to where you need it. Easily roll this cart through doorways and over thresholds. The trolley features four solid castor wheels, of which the two front wheels are equipped with a brake.

Neomounts NS-M1500BLACK has one pivot point and is suitable for screens up to 65" (165 cm). The weight capacity of this product is 50 kg each screen. The stand is suitable for screens that meet VESA hole pattern 200x200 to 600x400mm.

All installation material is included with the product.