

August 2024

PRODUCT DATA SHEET

Product Name:	LED tea lights
Supplier Code:	1105-12
Description:	Set of 12 battery operated tea lights. LED unit flickers to imitate a burning candle. Tea light will fit into a standard tea light holder. A safe alternative to traditional tea lights, providing a similar effect without the risks associated with naked flames.
Intended use:	Indoor lighting
Battery Type:	3V CR2032 button cell (supplied)
Battery Chemistry:	Lithium / Manganese Dioxide (Li/MnO ₂)
Battery Life:	40 – 60 hours
IP rating:	IP20
Construction:	Each tea light has a diameter of 38mm and overall height of 38mm. On/off switch is located on base of tea light. Material – ABS plastic
Edges, sharp points:	There are no burrs, sharp edges, or points.
Other:	No highly flammable materials present. No special precautions necessary.
Safety:	Not suitable for children under 3 years due to small parts. Always use under adult supervision.
Volume & weight:	Packed in a white faced cardboard box Packed Dimensions: 156mm x 120mm x 45mm Gross Weight: 0.192kg Qty / Carton: 48
EAN:	5060098477790