

2.54mm PCB connectors

Order code	Manufacturer code	Description
22-2590	n/a	2W 0.156" STRAIGHT PIN HEADER (RC)
22-2595	n/a	3W 0.156" STRAIGHT PIN HEADER (RC)
22-2600	n/a	4W 0.156" STRAIGHT PIN HEADER (RC)
22-2605	n/a	5W 0.156" STRAIGHT PIN HEADER (RC)
22-2610	n/a	6W 0.156" STRAIGHT PIN HEADER (RC)
22-2620	n/a	8W 0.156" STRAIGHT PIN HEADER (RC)
22-2630	n/a	10W 0.156" STRAIGHT PIN HEADER (RC)

2.54mm PCB connectors	Page 1 of 2
The enclosed information is believed to be correct, Information may change 'without notice' due to product improvement. Users should ensure that the product is suitable for their use. E. & O. E.	Revision A 04/07/2003

0.156" STRAIGHT HEADER

SPECIFICATION

VOLTAGE RATING : AC, DC, 250V max

CURRENT RATING : 7A. max


APPLICABLE PC BOARD THICKNESS : .063" (1.6mm)

Material:



Post: Brass

Insulator: Nylon 6/6 UL 94V-2

Plating: Tin Plated



Recommended P.C.B. hole layout



Circuits	Dim A	Dim B
2	3.96	7.9
3	7.92	11.9
4	11.88	15.8
5	15.84	19.8
6	19.80	23.8
8	27.72	31.7
10	35.64	39.6