



Ordering information & specifications:

| Wire Range | Insulation O.D | Material | Finish | Qty/reel |
|------------|----------------|-----------------|------------------|----------|
| AWG#18-#24 | 3.10mm (max) | Brass | Tin-plated | 5,000pcs |
| AWG#18-#24 | 3.10mm (max) | Phosphor Bronze | Tin-plated | 5,000pcs |
| AWG#18-#24 | 3.10mm (max) | Brass | Gold-plated 1u" | 5,000pcs |
| AWG#18-#24 | 3.10mm (max) | Brass | Gold-plated 15u" | 5,000pcs |
| AWG#18-#24 | 3.10mm (max) | Phosphor Bronze | Gold-plated 15u" | 5,000pcs |

Note: E-Stamping before Tin-plated or Gold-plated

