





SPECIFICATION

- A. MATERIAL:
- 1.HOUSING: NYLON 66 FLAMMABILITY UL 94V-0
- 2.TERMINAL: COPPER ALLOY, TIN-PLATED
- B: CHARACTERISTICS:
1. RATING: 15A 250V~ NORTH AMERICA  
10A 250V~ EUROPE
- 2.INSULATION RESISTANCE: 100MΩ MIN, AT 500V DC
- 3.ELECTRIC STRENGTH: AC 2,000V FOR ONE MINUTE
- C: APPROVALS:
- UL, CUL, ENEC & CCC



PANEL CUT-OUT



| REV | DATE       | DOCUMENT | DESCRIPTION        |
|-----|------------|----------|--------------------|
| E   | 2024.07.30 | DGR24005 | 修改电流规格             |
| D   | 2021.04.28 | DGR21005 | 更改安规刻字             |
| C   | 2011.10.10 | DGR11008 | CHANGE SAFETY MARK |
| B   | 2008.11.25 | DGR08065 | CHANGE DIMENSION   |
| A   | 04-12-06   | DGR06039 | NEW REVISION       |

|                                                                                                                                             |                                                                                     |                      |                                                                                     |                 |
|---------------------------------------------------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|----------------------|-------------------------------------------------------------------------------------|-----------------|
| <br>华玮电子（东莞）有限公司<br>INALWAYS ELECTRONIC(DONGGUAN)CO.,LTD | PART NO.:<br>0718-1-PW-2BK                                                          |                      | NAME:<br>AC OUTLET 3P<br>(SNAP-IN)                                                  |                 |
|                                                                                                                                             | MATERIAL:<br>SEE ABOVE                                                              |                      | SPEC.:<br>IEC 60320-2-2<br>SHEET F                                                  |                 |
|                                                                                                                                             | APPROVED                                                                            | CHECKED              | DESIGNER                                                                            | NOTE:           |
|                                                                                                                                             |  |                      |  |                 |
| TOLERANCE UNLESS OTHERWISE MARKED<br>DIMENSION:<br>.000 : ±0.1<br>.00 : ±0.2<br>.0 : ±0.3                                                   |                                                                                     | UNIT<br>mm           | SCALE<br>1 : 1                                                                      | SHEET<br>1 of 1 |
| A                                                                                                                                           | 4                                                                                   | DOC NO:<br>S718-0007 |                                                                                     |                 |