

Series 9 DC915N

Wireless portable doorbell with range extender, sleep mode and push button – White

Never miss a visitor again with a Honeywell DC915N doorbell, thanks to a market-leading 5 year battery life, 100m audible range and 200m wireless range. It comes with Sleep mode so you can relax free from disturbance, while the innovative Halo light will alert you when the doorbell can't be heard. Link two doorbells together for even greater wireless coverage and peace of mind.



Pack Contents:

1 x Wireless Portable Doorbell, 1 x Wireless Push Button, 1 x CR2032 (3V) Battery, 1 x Quick Start Guide, 1 x Safety & Guarantee, 1 x Declaration of Conformity,

Key Features and Benefits:

Never miss a visitor or delivery - Place your portable doorbell anywhere in your home, with Honeywell ActivLink™ technology providing a reliable wireless range of up to 200m, while the maximum volume of 90dB can be heard up to 100m away. Link two doorbells together to boost your range up to 400m.

Disturbance Free - With adjustable volume and innovative Sleep/Mute mode, which mutes the doorbell indefinitely, or for a prescribed period of 3, 6, 9 or 12 hours, your family can relax free from disturbances during movie nights or nap times.

Visual Alerts - The innovative Halo Light and LED Strobe provide discreet but effective visual alerts which complement your chosen melody in loud environments, or help to alert you when the doorbell can't be heard.

Revolutionary design - Compact and beautifully designed in a harmonising palette of white and grey, our doorbells are designed with your home in mind.

Peace of mind - Peace of mind for visitors, thanks to a LED confidence light on the push button, and peace of mind for you, thanks to the Secret Knock function which plays a different melody, so you know if it's a family member or friend at the door. For total peace of mind, let Honeywell ActivLink™ interconnect your doorbell with Honeywell security accessories and Home Alarm Kits to build your own bespoke home alert and alarm system.

Reliability and Quality - Honeywell ActivLink™, using the 868MHz frequency, is our innovative wireless protocol which delivers greater range capability, extended battery life of up to 5 years, and improved connection reliability, all supported by our 2 year product quality guarantee.

Compact size with rich sound - All Honeywell doorbells benefit from digitally enhanced, crystal clear sound that carries well throughout the home and garden, packing market-leading sound quality into some deceptively small packages!

Easy To Install - All Honeywell doorbells come pre-linked and ready to install straight out of the box, with optional screw-free installation and an easy open battery compartment so you can be set up in minutes. All this is backed up by our 2 year product guarantee.

Specification:

Wireless Portable Doorbell	
Colour	White
Wall mounted option	Yes
Frequency	868Mhz
Wireless Range (m)*	200
Range Extender	Yes
Audible Range (Volume)	100m (90dB)
Melodies	8
Sound	Volume Control / Internal Siren / Sleep Mode and Mute
Visual Alerts	8 Colour Halo / LED Strobe
Low Battery Indicator	Yes
USB Power Specification	Optional external supply USB 5V 500mA
Battery Specification	4 x LR14 (C) 1.5V
Battery Life (Years)	5
Dimensions (mm) / Weight (g)	126 (h) x 126 (w) x 41.8 (d) / 264 (g)
Fixings	Brackets / Screws / Rawl Plugs

Wireless Push Button	
Colour	White
Wall mounted option	Yes
Frequency	868Mhz
Wireless Range (m)*	200
Low Battery Indicator	Yes
Push Button Design	Portrait
Confidence Light	Yes
Battery Specification	1 x CR2032 (3V)
Battery Life (Years)	2
IP Rating	IP55
Name Plate	No
Dimensions (mm) / Weight (g)	30 (h) x 70 (w) x 16 (d) / 23.5 (g)
Fixings	Brackets / Screws / Rawl Plugs

Pack	
EAN Code	5004100965592
Pack Dimensions (mm) / Weight (g)	216 (h) x 150 (w) x 70 (d) / 525 (g)
Standard Pack Quantity	4

* Measured in open field conditions, walls, ceilings and metal structures will reduce the maximum range.