

Series 3 DC313NBS

Wireless plug-in doorbell with volume control and push button – White

Simple, reliable and hassle-free, the Honeywell DC313NBS plug-in doorbell will never need new batteries, and comes with adjustable volume to suit your mood, as well as a LED strobe for added visual alerts. And thanks to Honeywell ActivLink™ technology providing a reliable wireless connection, you know the doorbell will always work.



Pack Contents:

1 x Wireless Plug-in Doorbell, 1 x Wireless Push Button, 1 x CR2032 (3V) Battery, 1 x Quick Start Guide, 1 x Safety & Guarantee, 1 x Declaration of Conformity,

Key Features and Benefits:

Never miss a visitor or delivery - Place your plug-in doorbell anywhere in your home, with Honeywell ActivLink™ technology providing a reliable wireless range of up to 150m, while the maximum volume of 84dB can be heard up to 80m away.

Disturbance Free - Easily adjust the volume to suit your family and mood, or when you simply want some quiet time.

Visual Alerts - The LED Strobe provides a discreet but effective visual alert which complements your chosen melody in loud environments, or helps to alert you when the doorbell can't be heard.

Revolutionary design - Compact and beautifully designed in a harmonising palette of white and grey, our doorbells are designed with your home in mind.

Peace of mind - Peace of mind for visitors, thanks to a LED confidence light on the push button, and peace of mind for you, thanks to the Secret Knock function which plays a different melody, so you know if it's a family member or friend at the door. For total peace of mind, let Honeywell ActivLink™ interconnect your doorbell with Honeywell security accessories and Home Alarm Kits to build your own bespoke home alert and alarm system.

Reliability and Quality - Honeywell ActivLink™, using the 868MHz frequency, is our innovative wireless protocol which delivers greater range capability, extended battery life of up to 2 years, and improved connection reliability, all supported by our 2 year product quality guarantee.

Compact size with rich sound - All Honeywell doorbells benefit from digitally enhanced, crystal clear sound that carries well throughout the home and garden, packing market-leading sound quality into some deceptively small packages!

Easy To Install - All Honeywell doorbells come pre-linked and ready to install straight out of the box, with optional screw-free installation and an easy open battery compartment so you can be set up in minutes. All this is backed up by our 2 year product guarantee.

Specification:

Wireless Plug-in Doorbell	
Colour	White
Wall mounted option	No
Frequency	868Mhz
Wireless Range (m)*	150
Range Extender	No
Audible Range (Volume)	80m (84dB)
Melodies	6
Sound	Volume Control / Internal Siren
Visual Alerts	LED Strobe
Power Specification	100-240V 50-60Hz 300mA
USB Charging	No
Dimensions (mm) / Weight (g)	110 (h) x 70 (w) x 64 (d) / 184 (g)

Wireless Push Button	
Colour	White
Wall mounted option	Yes
Frequency	868Mhz
Wireless Range (m)*	200
Low Battery Indicator	Yes
Push Button Design	Portrait
Confidence Light	Yes
Battery Specification	1 x CR2032 (3V)
Battery Life (Years)	2
IP Rating	IP55
Name Plate	No
Dimensions (mm) / Weight (g)	30 (h) x 70 (w) x 16 (d) / 23.5 (g)
Fixings	Brackets / Screws / Rawl Plugs

Pack	
EAN Code	5004100965455
Pack Dimensions (mm) / Weight (g)	216 (h) x 150 (w) x 83 (d)
Standard Pack Quantity	4

* Measured in open field conditions, walls, ceilings and metal structures will reduce the maximum range.