

## Series 3 DC313NHGBS

### Wireless portable and plug-in doorbell with volume control and push button – White

Simple, reliable and hassle-free, the Honeywell DC313NHGBS home and garden kit comes with adjustable volume to suit your mood, and a LED strobe for added visual alerts. Place the plug-in doorbell inside your home and take the portable doorbell with you into the garden, so you'll always know when someone's at the door.



### Pack Contents:

1 x Wireless Portable Doorbell, 1 x Wireless Plug-in Doorbell, 1 x Wireless Push Button, 1 x CR2032 (3V) Battery, 1 x Quick Start Guide, 1 x Safety & Guarantee, 1 x Declaration of Conformity,

### Key Features and Benefits:

**Home and Garden Kit** - Never miss a visitor again with this flexible home and garden kit. Place the plug-in doorbell inside your home and take the portable doorbell with you into the garden, so you'll always know when someone's at the door.

**Never miss a visitor or delivery** - Take your portable doorbell anywhere around your home and garden, with Honeywell ActivLink™ technology providing a reliable wireless range of up to 150m, while the maximum volume of 84dB can be heard up to 80m away.

**Disturbance Free** - Easily adjust the volume to suit your family and mood, or when you simply want some quiet time.

**Visual Alerts** - The LED Strobe provides a discreet but effective visual alert which complements your chosen melody in loud environments, or helps to alert you when the doorbell can't be heard.

**Revolutionary design** - Compact and beautifully designed in a harmonising palette of white and grey, our doorbells are designed with your home in mind.

**Peace of mind** - Peace of mind for visitors, thanks to a LED confidence light on the push button, and peace of mind for you, thanks to the Secret Knock function which plays a different melody, so you know if it's a family member or friend at the door. For total peace of mind, let Honeywell ActivLink™ interconnect your doorbell with Honeywell security accessories and Home Alarm Kits to build your own bespoke home alert and alarm system.

**Reliability and Quality** - Honeywell ActivLink™, using the 868MHz frequency, is our innovative wireless protocol which delivers greater range capability, extended battery life of up to 2 years, and improved connection reliability, all supported by our 2 year product quality guarantee.

**Compact size with rich sound** - All Honeywell doorbells benefit from digitally enhanced, crystal clear sound that carries well throughout the home and garden, packing market-leading sound quality into some deceptively small packages!

**Easy To Install** - All Honeywell doorbells come pre-linked and ready to install straight out of the box, with optional screw-free installation and an easy open battery compartment so you can be set up in minutes. All this is backed up by our 2 year product guarantee.

## Specification:

### Wireless Portable Doorbell

Colour	White
Wall mounted option	Yes
Frequency	868Mhz
Wireless Range (m)*	150
Range Extender	No
Audible Range (Volume)	80m (84dB)
Melodies	6
Sound	Volume Control / Internal Siren
Visual Alerts	LED Strobe
Low Battery Indicator	Yes
Battery Specification	4 x LR6 (AA) 1.5V
Battery Life (Years)	2
Dimensions (mm) / Weight (g)	110 (h) x 70 (w) x 42.5 (d) / 169 (g)
Fixings	Brackets / Screws / Rawl Plugs

### Wireless Plug-in Doorbell

Colour	White
Wall mounted option	No
Frequency	868Mhz
Wireless Range (m)*	150
Range Extender	No
Audible Range (Volume)	80m (84dB)
Melodies	6
Sound	Volume Control / Internal Siren
Visual Alerts	LED Strobe
Power Specification	100-240V 50-60Hz 300mA
USB Charging	No
Dimensions (mm) / Weight (g)	110 (h) x 70 (w) x 64 (d) / 184 (g)

### Wireless Push Button

Colour	White
Wall mounted option	Yes
Frequency	868Mhz
Wireless Range (m)*	200
Low Battery Indicator	Yes
Push Button Design	Portrait
Confidence Light	Yes
Battery Specification	1 x CR2032 (3V)
Battery Life (Years)	2
IP Rating	IP55
Name Plate	No

Dimensions (mm) / Weight (g)	30 (h) x 70 (w) x 16 (d) / 23.5 (g)
Fixings	Brackets / Screws / Rawl Plugs

<b>Pack</b>	
EAN Code	5004100965431
Pack Dimensions (mm) / Weight (g)	216 (h) x 315 (w) x 88 (d)
Standard Pack Quantity	4

\* Measured in open field conditions, walls, ceilings and metal structures will reduce the maximum range.