

## Series 3 DW313S

### Wired doorbell with volume control and LED strobe – White

Simple, reliable and hassle-free, the Honeywell DW313S wired doorbell comes with adjustable volume to suit your mood, and a LED strobe for added visual alerts. You can wire it to your existing push button in minutes, and with an audible range of up to 80m, you know you'll never miss a visitor again.



### Pack Contents:

1 x Wired Doorbell, 1 x Quick Start Guide, 1 x Safety & Guarantee, 1 x Declaration of Conformity,

### Key Features and Benefits:

**Never miss a visitor or delivery** - Wire your existing push button to your wired doorbell, and you'll never miss a visitor again, thanks to a maximum volume of 84dB that can be heard up to 80m away.

**Disturbance Free** - Easily adjust the volume to suit your family and mood, or when you simply want some quiet time.

**Visual Alerts** - The LED Strobe provides a discreet but effective visual alert which complements your chosen melody in loud environments, or helps to alert you when the doorbell can't be heard.

**Revolutionary design** - Compact and beautifully designed in a harmonising palette of white and grey, our doorbells are designed with your home in mind.

**Peace of mind** - For added peace of mind, use a DCP917S wired to wireless converter kit to interconnect your doorbell with Honeywell security accessories and Home Alarm Kits to build your own bespoke home alert and alarm system.

**Reliability and Quality** - Enjoy an extended battery life of up to 2 years, supported by our 2 year product quality guarantee.

**Compact size with rich sound** - All Honeywell doorbells benefit from digitally enhanced, crystal clear sound that carries well throughout the home and garden, packing market-leading sound quality into some deceptively small packages!

**Easy To Install** - All Honeywell doorbells come pre-linked and ready to install straight out of the box, with optional screw-free installation and an easy open battery compartment so you can be set up in minutes. All this is backed up by our 2 year product guarantee.

## Specification:

### Wired Doorbell

Colour	White
Wall mounted option	Yes
Range Extender	No
Audible Range (Volume)	80m (84dB)
Melodies	6
Low Battery Indicator	Yes
Battery Specification	4 x LR6 (AA) 1.5V
Battery Life (Years)	2
Dimensions (mm) / Weight (g)	110 (h) x 70 (w) x 42.5 (d)

### Pack

EAN Code	5004100965707
Pack Dimensions (mm) / Weight (g)	216 (h) x 150 (w) x 55 (d)
Standard Pack Quantity	4

\* Measured in open field conditions, walls, ceilings and metal structures will reduce the maximum range.