

Series 3 DC311N

Wireless portable doorbell with push button – White

Simple, reliable and hassle-free, the Honeywell DC311N doorbell is everything you're looking for, and more. Pre-linked and ready to go out of the box, with a reliable wireless connection and great sound quality, you know you'll never miss a visitor again.



Pack Contents:

1 x Wireless Portable Doorbell, 1 x Wireless Push Button, 1 x CR2032 (3V) Battery, 1 x Quick Start Guide, 1 x Safety & Guarantee, 1 x Declaration of Conformity,

Key Features and Benefits:

Never miss a visitor or delivery - Take your portable doorbell anywhere around your home and garden, with Honeywell ActivLink™ technology providing a reliable wireless range of up to 150m, while the maximum volume of 80dB can be heard up to 60m away.

Revolutionary design - Compact and beautifully designed in a harmonising palette of white and grey, our doorbells are designed with your home in mind.

Peace of mind - Peace of mind for visitors, thanks to a LED confidence light on the push button, and peace of mind for you, thanks to the Secret Knock function which plays a different melody, so you know if it's a family member or friend at the door. For total peace of mind, let Honeywell ActivLink™ interconnect your doorbell with Honeywell security accessories and Home Alarm Kits to build your own bespoke home alert and alarm system.

Reliability and Quality - Honeywell ActivLink™, using the 868MHz frequency, is our innovative wireless protocol which delivers greater range capability, extended battery life of up to 2 years, and improved connection reliability, all supported by our 2 year product quality guarantee.

Compact size with rich sound - All Honeywell doorbells benefit from digitally enhanced, crystal clear sound that carries well throughout the home and garden, packing market-leading sound quality into some deceptively small packages!

Easy To Install - All Honeywell doorbells come pre-linked and ready to install straight out of the box, with optional screw-free installation and an easy open battery compartment so you can be set up in minutes. All this is backed up by our 2 year product guarantee.

Specification:

Wireless Portable Doorbell

| | |
|------------------------------|---------------------------------------|
| Colour | White |
| Wall mounted option | Yes |
| Frequency | 868Mhz |
| Wireless Range (m)* | 150 |
| Range Extender | No |
| Audible Range (Volume) | 60m (80dB) |
| Melodies | 4 |
| Sound | Internal Siren |
| Low Battery Indicator | Yes |
| Battery Specification | 4 x LR6 (AA) 1.5V |
| Battery Life (Years) | 2 |
| Dimensions (mm) / Weight (g) | 110 (h) x 70 (w) x 42.5 (d) / 169 (g) |
| Fixings | Brackets / Screws / Rawl Plugs |

Wireless Push Button

| | |
|------------------------------|-------------------------------------|
| Colour | White |
| Wall mounted option | Yes |
| Frequency | 868Mhz |
| Wireless Range (m)* | 200 |
| Low Battery Indicator | Yes |
| Push Button Design | Portrait |
| Confidence Light | Yes |
| Battery Specification | 1 x CR2032 (3V) |
| Battery Life (Years) | 2 |
| IP Rating | IP55 |
| Name Plate | No |
| Dimensions (mm) / Weight (g) | 30 (h) x 70 (w) x 16 (d) / 23.5 (g) |
| Fixings | Brackets / Screws / Rawl Plugs |

Pack

| | |
|-----------------------------------|----------------------------|
| EAN Code | 5004100965349 |
| Pack Dimensions (mm) / Weight (g) | 216 (h) x 150 (w) x 68 (d) |
| Standard Pack Quantity | 4 |

* Measured in open field conditions, walls, ceilings and metal structures will reduce the maximum range.