



**HEADER (FOR PRINTED CIRCUIT  
BOARDS) STRAIGHT SOLDER PIN,  
1X1 MM / 0.039X 0.039 IN PIN  
SPACING 5 MM / 0.197 IN  
231-132/001-000 TO 231-154/001-000**

|                                                             |                                           |
|-------------------------------------------------------------|-------------------------------------------|
| <b>ITEM-NO. (ITEM-NO.)</b>                                  | 231-145/001-000                           |
| <b>Measured voltage (Measured voltage / V)</b>              | 320                                       |
| <b>Measured shock voltage (Measured shock voltage / kV)</b> | 4                                         |
| <b>Pollution degree (Pollution degree)</b>                  | 2                                         |
| <b>Current intensity (Current intensity / A)</b>            | 12                                        |
| <b>RM (PIN SPACING / mm)</b>                                | 5                                         |
| <b>P (NO. OF POLES)</b>                                     | 15                                        |
| <b>Height (Height / mm)</b>                                 | 12                                        |
| <b>Width (Width / mm)</b>                                   | 78.2                                      |
| <b>Depth (Depth / mm)</b>                                   | 8.4                                       |
| <b>COLOR (COLOR)</b>                                        | grau                                      |
| <b>Comment (Comment)</b>                                    | L = (No. of poles x Pin Spacing) + 3,2 mm |
| <b>Dimensions (Dimensions)</b>                              | 1,4 +0,1 mm                               |