



**1. Specifications:**

Contact resistance: 30mΩ max.  
 Insulation resistance: 1000MΩ min. DC 500V Current rating: 1.5A  
 Voltage rating: 30V AC/DC  
 Dielectric strength: AC 500V for 1 minute

**2. Materials:**

Housing: PBT + 30% glass fiber (UL 94 - 0)  
 Contact: Copper alloy  
 Shell: Copper alloy



Recommend PCB Layout  
 Tolerance =  $\pm 0.05$

