

## **DATASHEET**

Φ22 mm, USB2.0 Female A – Male A with 150 cm cable, Version 05/16 silver surface, Ring illuminated

BN no. 1457893 (Silver surface) 1457894 (Black surface)



10MAX: means the panel thickness, the max thickness for the panel no more than 10mm.

Specification	USB2.0 Female A – Male A with 150 cm cable,
Mounting diameter	22 mm
LED colour	White circle illuminated
Body material	PC
Cap colour	silver cap or black cap
Transmission Speed	≥ 30 MB/s
Operating and storage temperature	20 to +55 °C
Operating and storage humidity	10 to 85 % RH
Panel thickness	1 ~ 10 mm



This data sheet is a publication by Conrad Electronic SE, Klaus-Conrad-Str. 1, D-92240 Hirschau (www.conrad.com). All rights including translation reserved. Reproduction by any method, e.g. photocopy, microfilming, or the capture in electronic data processing systems require the prior written approval by the editor. Reprinting, also in part, is prohibited. This data represent the technical status at the time of printing. Changes in technology and equipment reserved.

<sup>©</sup> Copyright 2016 by Conrad Electronic SE.