




Data Sheet

USB A x 2 with protective cap, surface mount, open end wire

Voltage	12V/24V DC	Mounting Hole
Output	5V DC 3.1A MAX	
Max Output Power	15.5W Max	
Approvals		
Operating Temperatures	-30°C ~ +45°C 	

1. Tolerances ± 0.3 Unless Otherwise Specified

A4

09/09/22							
Date	Name	Description					No.
Drawn	Checked	Approved	SCI BOM No.		Model Name	USB Sockets	
			Customer No.		Model No.		Rev.
09/09/22	2022/09/09	2022/09/09	Unit	mm			1