

3Doodler Create

In the box:

- 3Doodler Create pen
- US, UK, EU, AUS, KR, JP or BR power adaptor
- Mini screw-driver
- Mini spanner
- Unblocking tool
- 50-strands of plastic (x2 mixed packs)



Product Dimensions

Pen Dimensions:

	L	W	H
cm	1.7	1.9	15.6
inches	0.67	0.75	6.14

Packaging Dimensions:

	L	W	H
cm	12.8	7.8	28.6
inches	5.04	3.07	11.26

Carton Dimensions (case pack of 20 units):

	L	W	H
cm	54	30	42
inches	21.26	11.81	16.54

Product Weight

Item	g/kg	oz/lb
Pen only	50g	1.76oz
Full product / boxed	595g	20.99oz
G.W. per carton (20 units)	12.70kg	28.00lbs
N.W. per carton (20 units)	11.90kg	26.24lbs



Additional Data / Tech Specs

HS Code: 8516.79.0000 "Electromechanical tools for working in the hand"

Power Supply:

- Universal power supply 110V~240V, UL rated, output: 5V, 1.2A (6W)
- 6ft power cord

Heater Information:

- Warm up time: 1:20~1:30 mins
- Heater time-out: after 5 min of no activity the heating element will be powered down
- HIGH setting = 200~230°C (Blue LED)
- LOW setting = 180~200°C (Red LED)

New Features:

- Anodized aluminium casing
- Double click for continuous flow
- Lower power consumption
- Redesigned drive system

Control Port Information:

- A small 3-pin port that is connected to the buttons using 3Doodler accessories (like the Pedal)
- Instructions can be found here: <http://the3doodler.com/2014/03/26/three-pin-control-port>

Compliance Information

FCC & CE compliant; fully certified UL/CUL power adaptors, including local certifications.