





NOTE: FINISH (PLATING THICKNESS IN MICRO-INCHES)

1. BRASS PER JIS-C3804
2. TEFLON MIL-P-19468
3. CONNECTOR INTERFACE PER MIL-STD-348A
4. PART TO BE CLEAN AND FREE BURRS
5. NICKEL PL 70 μ " THICK OVER COPPER STRIKE
6. GOLD PL 1-3 μ " OVER NICKEL PL 70 μ " THICK OVER COPPER STRIKE

7	Braid Clamp	Brass	Silver
6	Gasket	Rubber	Red
5	Nut	Brass	Nickel
4	Shell	Brass	Nickel
3	Insulator	Teflon	White
2	Contact	Brass	Gold
1	Body	Brass	Nickel
No	Description	Material	Finish



DIMENSIONS ARE IN MILLIMETERS

251305

RoHS COMPLIANT

UNLESS OTHERWISE SPECIFIED

TOLERANCES
 0.5-6=±0.2
 6-30=±0.4
 30-120=±0.6
 120-315=±1.0
 315-1000=±1.6
 1000-2000=±2.4

PART NO.

0401235

TITLE: BNC CLAMP PLUG FOR AIRCELL7 CABLE

DATE

May / 18 / 2010

NOT SCALED DRAWING

DRAWING NO.