


Impedance	50Ω
Frequency range	0-6 GHz
Voltage rating	1500 volts peak
Dielectric withstanding voltage	2500 volts rms
VSWR	M39012 straight connectors:1.3max,0-11GHz M39012 right angle:1.35 max,0-11GHz
othr (MIL-C-39012 cable connectors)	Contact resistance: center contact 1.0 milliohm outer contact 0.2 milliohm insertion loss:0.15db max at 10.0GHz insulation resistance:5000 megohms(min)

5	Shell	Brass	Nickel
4	Gasket	Rubber	Red
3	Insulator	Delrin	White
2	Contact	Brass	Gold
1	Body	Brass	Nickel
No	Description	Material	Finish



- NOTES: FINISH (PLATING THICKNESS IN MICRO-INCHES)
1. BODY: BRASS PER JIS-C3604
  2. CONTACT: BRASS PER JIS-C3604
  3. CONNECTOR INTERFACE PER MIL-STD-348A
  4. PART TO BE CLEAN AND FREE BURRS
  5. NICKEL PL 70 MIN THICK OVER COPPER STRIKE
  6. GOLD PL 3 MIN OVER NICKEL PL 70 MIN THICK OVER COPPER STRIKE

Artikelnummer    Artikeltext  
 252549            Winkel-Adapter, N-Stecker auf N-Stecker, 50 ?