


Order code	Manufacturer code	Description
26-1584	R3-43C BLACK	INLINE AUTOMOTIVE FUSE HOLDER 15A(RC)

	Page 1 of 2
The enclosed information is believed to be correct, Information may change without notice due to product improvement. Users should ensure that the product is suitable for their use. E. & O. E.	Revision A 20/02/2007



SPECIFICATIONS :

- A. Rated Current : 15A
- B. Insulation Resistance At 500V DC : 100MΩ Min.
- C. Contact Resistance : 5 mΩ At 1A DC
- D. Dielectric Strength For 60 Seconds : AC 1000V Min.
- E. Body Material : P.V.C.
- F. Supply Standard UL Wire-AWG/Length : 16# AWG/ 4" x 2

* Contact : Brass, Tin/Nickel Plated

* With Other Wire Size Or Lengths Available On Special Order

* To Install Fuses With " Loop " Type Wires, Simply Cut Loop Into Two Form Separate Wires Of Desired Length.

TOLERANCE: ±0.2mm UNLESS OTHERWISE SPECIFIED.

					△	
					△	
Date	Name	Description				NO
Drawn	Checked	Approved	SCI BOM No.	1310196	Model Name	FUSE HOLDER
曹盈芳		<i>[Signature]</i>	Customer No.		Model No.	R3-43CK
06/10/'09		<i>[Signature]</i>	Unit	mm	SHIN CHIN INDUSTRIAL CO., LTD.	
						REV. 0