




THIS DOCUMENT IS THE PROPERTY OF
KEYSTONE ELECTRONICS CORP. AND
SHALL NOT BE REPRODUCED, DISTRIBUTED
OR USED AS A BASIS FOR MANUFACTURE
WITHOUT PRIOR WRITTEN PERMISSION
FROM KEYSTONE ELECTRONICS CORP.

MOUNTING LAYOUT



NOTE:

CLIP: .016 [0.40] TH'K BRASS, TIN NICKEL PLATE
BASE: MAT'L: GLASS FILLED NYLON, UL 94V-0
CURRENT RATING: 30 AMPS
VOLTAGE RATING: 500VAC
TEMPERATURE RATING: -58°F TO +292°F
(-50°C TO +145°C)

3.0512	CHANGE AS PER ECN 12-029	F
8.18.06	CHANGE AS PER ECN 06-046	E
9.21.04	CHANGE AS PER ECN 04-121	D
DATE	DESCRIPTION	REV.

KEYSTONE ELECTRONICS CORP.			
www.keyelco.com • ASTORIA, N.Y. 11105-2017 • Tel (718) 956-8900			
PART NAME			
PC AUTO FUSE SOCKET			
MATERIAL			
AS NOTED			
FINISH		DRN BY	BOONE
AS NOTED		DATE	10.5.92
		APP'D	LN
		SCALE	4X
TOLERANCES	INCH [MM]	CODE	DWG NO.
DECIMAL	± .005 [± 0.15]	C	
ANGULAR	± 1°		
UNLESS OTHERWISE SPECIFIED			

3522-2