

Specifications:

Metal material:	Spring brass
Insertion & extraction force:	1Kg min.
Dielectric strength for 60 seconds:	AC 500V min.
Suitable rated current:	15A 250V
Insulation resistance at 500V DC:	100MΩ min.
Temperature rise:	50°C max.
Voltage drop:	20mV max.
Body material:	Flame retarding UL 94V0 thermoplastic material
Metal finish:	Bright tin plated = CQ-122 Nickel plating = CQ-122N

