

Rapid Part Number: **28-3974**

Europa Part Number: **SSTB404020**

Specifications and dimensions



- Steel enclosure with brushed finish
- Back plate included

Features	
External height	400mm
External width	400mm
External depth	200mm
Steel thickness	1.2mm
Weight	9.5Kg
Degree of protection	IP65
Colour	RAL7035
Number of locks	1
Mounting plate width	345mm
Mounting plate height	345mm
Mounting plate thickness	2 to 2.5 mm
Internal depth	175mm
Number of top gland plates	1
Number of bottom gland plates	1
Gland plate aperture width	215mm
Gland plate aperture depth	62mm
Related Products	
Key lock	STBKEYLOCK
Wall mounting brackets (4)	STBRACKET
Spare plastic key	STBKEY010
Extension Box	STBEX204020
Weather Hood	STBWH104020

ⓘ ALL PRODUCTS, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE.

Information provided in data sheets and/or specifications may vary from actual results in different applications and performance may vary over time. **All products must be installed according to manufacturers instructions.**

Europa House, Airport Way, Luton, Beds, LU2 9NH Tel: 01582 692 440 / Fax: 01582 692 450 e-mail: sales@europacomponents.com
website: <http://www.europacomponents.com>