



Rapid Part Number: 28-3975

Europa Part Number: SSTB504020

Specifications and dimensions

Steel enclosure with brushed finish

Back plate included





Buck place meladed	
Features	
External height	500mm
External width	400mm
External depth	200mm
Steel grade	304
Steel thickness	1.2mm
Weight	10.5Kg
Degree of protection	IP65
Number of locks	1
Mounting plate width	340mm
Mounting plate height	540mm
Mounting plate thickness	2 to 2.5 mm
Internal depth	180mm
Related Products	
Key lock	STBKEYLOCK
Spare plastic key	STBKEY010

(1) ALL PRODUCTS, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE.

Information provided in data sheets and/or specifications may vary from actual results in different applications and performance may vary over time. All products must be installed according to manufacturers instructions.

Europa House, Airport Way, Luton, Beds, LU2 9NH Tel: 01582 692 440 / Fax: 01582 692 450 e-mail: sales@europacomponents.com website: http://www.europacomponents.com