



Rapid Part Number: **28-4272**
 Europa Part Number: **STB403015**
 Specifications and dimensions

- Steel Enclosure Coated with Epoxy Polyester Powder Textured Finish
- Top and Bottom Gland Plates and Backplate Included

Features	
External height	400mm
External width	300mm
External depth	150mm
Steel thickness	1.2mm
Weight	6.5Kg
Degree of protection	IP65
Colour	RAL7035
Number of locks	1
Mounting plate width	245mm
Mounting plate height	345mm
Mounting plate thickness	2 to 2.5 mm
Internal depth	125mm
Number of top gland plates	1
Number of bottom gland plates	1
Gland plate aperture width	180mm
Gland plate aperture depth	62mm
Related Products	
Key lock	STBKEYLOCK
Wall mounting brackets (4)	STBRACKET
Spare plastic key	STBKEY010

ⓘ ALL PRODUCTS, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE.

Information provided in data sheets and/or specifications may vary from actual results in different applications and performance may vary over time. **All products must be installed according to manufacturers instructions.**

Europa House, Airport Way, Luton, Beds, LU2 9NH Tel: 01582 692 440 / Fax: 01582 692 450 e-mail: sales@europacomponents.com
 website: <http://www.europacomponents.com>