

Rapid Part Number: **28-4284**

Europa Part Number: **STB605030**

Specifications and dimensions



- Steel enclosure with epoxy polyester powder textured finish
- Top and bottom gland plates and back plate included

| Features | |
|-------------------------------|-------------|
| External height | 600mm |
| External width | 500mm |
| External depth | 300mm |
| Steel thickness | 1.2mm |
| Weight | 17.6Kg |
| Degree of protection | IP65 |
| Colour | RAL7035 |
| Number of locks | 2 |
| Mounting plate width | 545mm |
| Mounting plate height | 445mm |
| Mounting plate thickness | 2 to 2.5 mm |
| Internal depth | 275mm |
| Number of top gland plates | 1 |
| Number of bottom gland plates | 1 |
| Gland plate aperture width | 415mm |
| Gland plate aperture depth | 120mm |
| Related Products | |
| Key lock | STBKEYLOCK |
| Wall mounting brackets (4) | STBRACKET |
| Spare plastic key | STBKEY010 |

ⓘ ALL PRODUCTS, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE.

Information provided in data sheets and/or specifications may vary from actual results in different applications and performance may vary over time. **All products must be installed according to manufacturers instructions.**

Europa House, Airport Way, Luton, Beds, LU2 9NH Tel: 01582 692 440 / Fax: 01582 692 450 e-mail: sales@europacomponents.com
 website: <http://www.europacomponents.com>