

Rapid Part Number: **28-4288**
 Europa Part Number: **STB705025**
 Specifications and dimensions



- Steel enclosure with epoxy polyester powder textured finish
- Top and bottom gland plates and back plate included

Features	
External height	700mm
External width	500mm
External depth	250mm
Steel thickness	1.2mm
Weight	20Kg
Degree of protection	IP65
Colour	RAL7035
Number of locks	2
Mounting plate width	445mm
Mounting plate height	640mm
Mounting plate thickness	2 to 2.5 mm
Internal depth	225mm
Number of top gland plates	1
Number of bottom gland plates	1
Gland plate aperture width	415mm
Gland plate aperture depth	120mm
Related Products	
Key lock	STBKEYLOCK
Wall mounting brackets (4)	STBRACKET
Spare plastic key	STBKEY010

ⓘ ALL PRODUCTS, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE.

Information provided in data sheets and/or specifications may vary from actual results in different applications and performance may vary over time. **All products must be installed according to manufacturers instructions.**

Europa House, Airport Way, Luton, Beds, LU2 9NH Tel: 01582 692 440 / Fax: 01582 692 450 e-mail: sales@europacomponents.com
 website: <http://www.europacomponents.com>