









top and bottom glnd paltes and backplate included

Features	
External height	200mm
External width	600mm
External depth	300mm
Steel thickness	1.2mm
Weight	5.15 Kg
Degree of protection	IP65
Colour	RAL7035
Mounting plate width	545mm
Mounting plate height	145mm
Mounting plate thickness	2 to 2.5 mm
Internal depth	275mm
Number of top gland plates	1
Number of bottom gland plates	1
Gland plate aperture width	580mm
Gland plate aperture depth	260mm
Related Products	
Enclosure range	STB
Safe Switch range	LB

(1) ALL PRODUCTS, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE.

Information provided in data sheets and/or specifications may vary from actual results in different applications and performance may vary over time. All products must be installed according to manufacturers instructions.

Europa House, Airport Way, Luton, Beds, LU2 9NH Tel: 01582 692 440 / Fax: 01582 692 450 e-mail: sales@europacomponents.com website: http://www.europacomponents.com