

Rapid Part Number: **28-4326**

Europa part Number: **LB254PSS**

Specifications and dimensions

- Boxed isolator 4 pole
- Metal plastic enclosure with padlockable handle
- Stainless steel construction



Specifications	
Height	173mm
Width	100mm
Depth	120mm
Depth including switch	164mm
Degree of protection	IP65
Stainless steel grade	304
Rated operational current Ie AC21A	25A
Rated operational current Ie AC22A	20A
Rated operational voltage Ue IEC & EN	690V
Rated operational power AC23A 380-440V	11kW
Rated operational power AC3 440V	7.5kW
Maximum gL fuse size IEC	20A
Rated fused short circuit capacity IEC	5kA
Normal operating temperature	-25°C to +40°C
Maximum cable capacity	6mm <sup>2</sup>
Recommended tightening torque	1.7Nm
Number of possible auxilliary contacts	None

ⓘ ALL PRODUCTS, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE.

Information provided in data sheets and/or specifications may vary from actual results in different applications and performance may vary over time. **All products must be installed according to manufacturers instructions.**

Europa House, Airport Way, Luton, Beds, LU2 9NH Tel: 01582 692 440 / Fax: 01582 692 450 e-mail: sales@europacomponents.com  
 website: <http://www.europacomponents.com>