

Rapid Part Number: **28-4330**
 Europa Part Number: **LB804PSS**
 Specifications and dimensions



- Boxed isolator 4 pole
- Metal plastic enclosure with padlockable handle
- Stainless steel construction



Specifications	
Height	178mm
Width	178mm
Depth	135mm
Depth including switch	179mm
Degree of protection	IP65
Stainless steel grade	304
Rated operational current Ie AC21A	80A
Rated operational current Ie AC22A	63A
Rated operational voltage Ue IEC & EN	690V
Rated operational power AC23A 380-440V	37kW
Rated operational power AC3 440V	22kW
Maximum gL fuse size IEC	63A
Rated fused short circuit capacity IEC	30kA
Normal operating temperature	-25°C to +40°C
Maximum cable capacity	25mm ²
Recommended tightening torque	2.0Nm
Number of possible auxilliary contacts	1
Related products	
Neutral contact (early make/late break)	LB280AUXEM
Volt free contact 1NO + 1NC	LBAC125RM
Volt free contact 2NO	LBAC125RM2NO

ⓘ ALL PRODUCTS, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE.

Information provided in data sheets and/or specifications may vary from actual results in different applications and performance may vary over time. **All products must be installed according to manufacturers instructions.**

Europa House, Airport Way, Luton, Beds, LU2 9NH Tel: 01582 692 440 / Fax: 01582 692 450 e-mail: sales@europacomponents.com
 website: <http://www.europacomponents.com>