



Rapid Part Number: **28-4339**  
 Europa Part Number: **LB634PSTB**  
 Specifications and dimensions



- Boxed isolator 4 pole
- Metal enclosure with padlockable handle
- Epoxy coated steel construction

Specifications	
Height	220mm
Width	145mm
Depth	90mm
Depth including switch	134mm
Degree of protection	IP54
Colour of base	RAL7043
Colour of Lid	RAL7032
Rated operational current Ie AC21A	63A
Rated operational current Ie AC22A	40A
Rated operational voltage Ue IEC & EN	690V
Rated operational power AC23A 380-440V	18.5kW
Rated operational power AC3 440V	11kW
Maximum gL fuse size IEC	63A
Rated fused short circuit capacity IEC	30kA
Normal operating temperature	-25°C to +40°C
Maximum cable capacity	10mm <sup>2</sup>
Recommended tightening torque	2Nm
Number of possible auxilliary contacts	1
Related products	
Neutral contact (early make/late break)	LB263AUXEM
Volt free contact 1NO + 1NC	LBAC16RM
Volt free contact 2NO	LBAC16RM2NO

ⓘ ALL PRODUCTS, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE.

Information provided in data sheets and/or specifications may vary from actual results in different applications and performance may vary over time. **All products must be installed according to manufacturers instructions.**

Europa House, Airport Way, Luton, Beds, LU2 9NH Tel: 01582 692 440 / Fax: 01582 692 450 e-mail: sales@europacomponents.com  
 website: <http://www.europacomponents.com>