



Rapid Part Number: 28-4367 Europa Part Number: **LBC1002P** 

Specifications and dimensions

Changeover switch 2 pole

ABS plastic enclosure with lockable handle





Specifications	
Height	254mm
Width	180mm
Depth	137mm
Depth including switch	178mm
Degree of protection	IP65
Rated operational current le AC22A	100A
Rated insulation voltage Ui	690V
Rated impulse withstand voltage Ump	8kV
Normal operating temperature	-25°C to +40°C
Maximum cable capacity	50mm <sup>2</sup>

(i) ALL PRODUCTS, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE.

Information provided in data sheets and/or specifications may vary from actual results in different applications and performance may vary over time. All products must be installed according to manufacturers instructions.

Europa House, Airport Way, Luton, Beds, LU2 9NH Tel: 01582 692 440 / Fax: 01582 692 450 e-mail: sales@europacomponents.com website: http://www.europacomponents.com

Page 1 of 1 **EPC**1528-001RA