

Rapid Part Number: **28-4450**
 Europa Part Number: **EUC1P20C**
 Specifications and dimensions



- Miniature Circuit Breakers
- Din rail mounted for use on 230/240V AC

Features	
Width	17.5mm
Height (overall)	82mm
Depth (overall)	76mm
Weight	0.11Kg
Standard	EN60898
Degree of protection	IP20
Rated voltage Ue	240V AC
Number of poles	1
Rated impulse withstand voltage Uimp	4kV
Current ratings A	20
Rated short circuit capacity Icn	10kA
Characteristic curve	C
Instantaneous trip current	3-5 times full load current
Maximum cable capacity	25mm ²
Recommended tightening torque	2.0Nm
Related Products	
Other Amperages in the Range	1, 2, 4, 6, 10, 16, 25, 32, 40, 50, 63
Locking device	EUBLOCK
Padlock	EUBPADLOCK
Auxilliary switch	EUCA11

ⓘ ALL PRODUCTS, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE.

Information provided in data sheets and/or specifications may vary from actual results in different applications and performance may vary over time. **All products must be installed according to manufacturers instructions.**

Europa House, Airport Way, Luton, Beds, LU2 9NH Tel: 01582 692 440 / Fax: 01582 692 450 e-mail: sales@europacomponents.com
 website: <http://www.europacomponents.com>