



Rapid Part Number: **28-4468**
 Europa Part Number: **EUC2P1C**
 Specifications and dimensions

- Miniature Circuit Breakers
- Din rail mounted for use on 230/240V AC

| Features | |
|--------------------------------------|---|
| Current Ratings A | 1 |
| Width | 35mm |
| Height (overall) | 82mm |
| Depth (overall) | 76mm |
| Weight | 0.11Kg |
| Standard | EN60898 |
| Degree of protection | IP20 |
| Rated voltage Ue | 240V AC |
| Number of poles | 2 |
| Rated impulse withstand voltage Uimp | 4kV |
| Rated short circuit capacity Icn | 10kA |
| Characteristic curve | C |
| Instantaneous trip current | 5-10 times full load current |
| Maximum cable capacity | 25mm ² |
| Recommended tightening torque | 2.0Nm |
| Related Products | |
| Other Amperages in the Range | 2, 4, 6, 10, 16, 20, 25, 32, 40, 50, 63 |
| Locking device | EUBLOCK |
| Padlock | EUPADLOCK |
| Auxilliary switch | EUCA11 |

ⓘ ALL PRODUCTS, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE.

Information provided in data sheets and/or specifications may vary from actual results in different applications and performance may vary over time. **All products must be installed according to manufacturers instructions.**

Europa House, Airport Way, Luton, Beds, LU2 9NH Tel: 01582 692 440 / Fax: 01582 692 450 e-mail: sales@europacomponents.com
 website: <http://www.europacomponents.com>