



Rapid Part Number: **28-4482**Europa Part Number: **EUC2P4D**Specifications and dimensions





- Miniature Circuit Breakers
- Din rail mounted for use on 230/240V AC

Features	
Current Ratings A	4
Width	35mm
Height (overall)	82mm
Depth (overall)	76mm
Weight	0.11Kg
Standard	EN60898
Degree of protection	IP20
Rated voltage Ue	240V AC
Number of poles	2
Rated impulse withstand voltage Uimp	4kV
Rated short circuit capacity Icn	10kA
Characteristic curve	D
Instantaneous trip current	5-10 times full load current
Maximum cable capacity	25mm²
Recommended tightening torque	2.0Nm
Related Products	·
Other Amperages in the Range	1, 2, 6, 10, 16, 20, 25, 32, 40, 50, 63
Locking device	EUBLOCK
Padlock	EUBPADLOCK
Auxilliary switch	EUCA11

(1) ALL PRODUCTS, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE.

Information provided in data sheets and/or specifications may vary from actual results in different applications and performance may vary over time. All products must be installed according to manufacturers instructions.

Europa House, Airport Way, Luton, Beds, LU2 9NH Tel: 01582 692 440 / Fax: 01582 692 450 e-mail: sales@europacomponents.com website: http://www.europacomponents.com

Page 1 of 1

EPC2020-001RA