



Rapid Part Number: **28-4500**Europa Part Number: **EUC3P32B**Specifications and dimensions

JC3P32B



- Miniature Circuit Breakers
- Din rail mounted for use on 230/240V AC

| Features | |
|--------------------------------------|--|
| Current Rating A | 32 |
| Width | 55mm |
| Height (overall) | 82mm |
| Depth (overall) | 76mm |
| Weight | 0.34Kg |
| Standard | EN60898 |
| Degree of protection | IP20 |
| Rated voltage Ue | 240V AC |
| Number of poles | 3 |
| Rated impulse withstand voltage Uimp | 4kV |
| Other amperages in the range | 1, 2, 4, 6, 10, 16, 20, 25, 40, 50, 63 |
| Rated short circuit capacity Icn | 10KA |
| Characteristic curve | В |
| Instantaneous trip current | 3-5 times full load current |
| Maximum cable capacity | 25mm² |
| Recommended tightening torque | 2.0Nm |
| Related Products | |
| Locking device | EUBLOCK |
| Padlock | EUBPADLOCK |
| Auxilliary switch | EUCA11 |

(1) ALL PRODUCTS, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE.

Information provided in data sheets and/or specifications may vary from actual results in different applications and performance may vary over time. All products must be installed according to manufacturers instructions.

Europa House, Airport Way, Luton, Beds, LU2 9NH Tel: 01582 692 440 / Fax: 01582 692 450 e-mail: sales@europacomponents.com website: http://www.europacomponents.com