

Rapid Part Number: **28-4528**
 Europa Part Number: **EUC7R.6/1B**
 Specifications and dimensions



- RCBO
- Single module



Dimensions	
Width	17mm
Height (overall)	113mm
Depth (overall)	76mm
Weight	0.21 Kg
Features	
Standard	EN61009
Degree of protection	IP20
Rated current I _n	6A
Rated Residual Operating Current I _{Δn}	30mA
Tripping characteristic class	B
Rated voltage U _e	240V AC
Number of poles	1
Rated short circuit capacity I _{cn}	10KA
Operating Temperature	.-5°C to +40°C
Degree of pollution	2
Maximum cable capacity	16mm ²
Recommended tightening torque	2.0Nm
Related Products	
Suitable 4 way plastic enclosure	ECW
Suitable 4 way metal enclosure	MEC

ⓘ ALL PRODUCTS, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE.

Information provided in data sheets and/or specifications may vary from actual results in different applications and performance may vary over time. **All products must be installed according to manufacturers instructions.**

Europa House, Airport Way, Luton, Beds, LU2 9NH Tel: 01582 692 440 / Fax: 01582 692 450 e-mail: sales@europacomponents.com
 website: <http://www.europacomponents.com>