

Rapid Part Number: **28-4542**

Europa Part Number: **EUR180.30/2**

Specifications and dimensions



*Image representative of range

- RCCB - Residual Current Circuit Breaker
- Two module



Dimensions	
Width	36mm
Height (overall)	90mm
Depth (overall)	76mm
Weight	0.22 Kg
Features	
Standard	EN61008
Degree of protection	IP20
Rated current In	80A
Rated Residual Operating Current I Δ n	30mA
Tripping time 1 x I Δ n	≤ 300ms
Tripping time 5 x I Δ n	≤ 40ms
Rated voltage Ue	110/230V
Number of poles	2
Rated short circuit capacity Icn	6kA
Operating Temperature	-.5°C to +40°C
Degree of pollution	2
Maximum cable capacity	25mm ²
Recommended tightening torque	2.0Nm
Related Products	
Suitable plastic enclosure	ECW
Suitable metal enclosure	MEC
Plastic consumer unit	ECU
Metal clad consumer unit	MECU

ⓘ ALL PRODUCTS, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE.

Information provided in data sheets and/or specifications may vary from actual results in different applications and performance may vary over time. **All products must be installed according to manufacturers instructions.**

Europa House, Airport Way, Luton, Beds, LU2 9NH Tel: 01582 692 440 / Fax: 01582 692 450 e-mail: sales@europacomponents.com
website: <http://www.europacomponents.com>