

Rapid Part Number: **28-4566**  
 Europa Part Number: **RCD13AMC**  
 Specifications and dimensions



- RCD Metal Clad Switched Socket
- Trip indicator
- Mechanically latching



Dimensions	
Width	152mm
Height (overall)	95mm
Depth (overall)	62mm
Weight	0.565Kg
Features	
Standard	BS 7288 and BS1363
Degree of protection	IP20
Rated current I <sub>n</sub>	13A
Rated Residual Operating Current I <sub>Δn</sub>	30mA
Trip speed	≤ 40 ms
Rated voltage U <sub>e</sub>	240V AC
Short circuit withstand	1500A
Number of poles	2
Operating Temperature	-.5°C to +40°C
Maximum cable capacity	5 x 2.5mm <sup>2</sup>
	2 x 4mm <sup>2</sup>
	1 x 6mm <sup>2</sup>

ⓘ ALL PRODUCTS, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE.

Information provided in data sheets and/or specifications may vary from actual results in different applications and performance may vary over time. **All products must be installed according to manufacturers instructions.**

Europa House, Airport Way, Luton, Beds, LU2 9NH Tel: 01582 692 440 / Fax: 01582 692 450 e-mail: sales@europacomponents.com  
 website: <http://www.europacomponents.com>