

Rapid Part Number: **28-4569**
 Europa Part Number: **RCD13ASS**
 Specifications and dimensions



- RCD Plastic Switched Socket
- Trip indicator
- Mechanically latching



Dimensions	
Width	152mm
Height (overall)	95mm
Depth (overall)	42mm
Weight	0.242Kg
Features	
Standard	BS 7288 and BS1363
Degree of protection	IP20
Rated current I _n	13A
Rated Residual Operating Current I _{Δn}	30mA
Trip speed	≤ 40 ms
Rated voltage U _e	240V AC
Short circuit withstand	1500A
Number of poles	2
Operating Temperature	.-5°C to +40°C
Maximum cable capacity	5 x 2.5mm ²
	2 x 4mm ²
	1 x 6mm ²
Minimum box depth	25mm

ⓘ ALL PRODUCTS, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE.

Information provided in data sheets and/or specifications may vary from actual results in different applications and performance may vary over time. **All products must be installed according to manufacturers instructions.**

Europa House, Airport Way, Luton, Beds, LU2 9NH Tel: 01582 692 440 / Fax: 01582 692 450 e-mail: sales@europacomponents.com
 website: <http://www.europacomponents.com>