



**Rapid Part Number: 28-4620**  
**Europa Part Number: TR2-D18321**  
 Specifications and dimensions

- Class 10 thermal overload relay for TC1 contactor range
- Connection by screw clamp direct to contactor or remote by mounting block
- With 1 NO and 1 NC auxilliary contacts

Dimensions	
Height	92mm
Width	44mm
Depth	47mm
Weight	0.183 Kg
Features	
Ingress Protection Rating	IP20
Ambient Temperature Storage	-60 to +70°C
Ambient Temperature Operating	-40 to +70°C
Maximum rated operational voltage	600V
Maximum contactor size	D38
Setting range	12 to 18 A
Terminal capacity flexible cable with ferrule	6mm <sup>2</sup>
Tightening torque	2.5 Nm
Tripping Threshold	1.14 ±0.06 In
Auxilliary Contact	
Thermal amperage	5A
Tightening torque	1.85 Nm
Terminal capacity flexible cable with ferrule	2.5mm <sup>2</sup>
Related Products	
Overload mounting plate	TA7-D0964

ⓘ ALL PRODUCTS, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE.

Information provided in data sheets and/or specifications may vary from actual results in different applications and performance may vary over time. **All products must be installed according to manufacturers instructions.**

Europa House, Airport Way, Luton, Beds, LU2 9NH Tel: 01582 692 440 / Fax: 01582 692 450 e-mail: sales@europacomponents.com  
 website: <http://www.europacomponents.com>