



Rapid Part Number: 28-4624
Europa Part Number: TR2-D40353
 Specifications and dimensions

- Class 10 thermal overload relay for TC1 contactor range
- Connection by screw clamp direct to contactor or remote by mounting block
- With 1 NO and 1 NC auxilliary contacts



Dimensions	
Height	109mm
Width	70mm
Depth	54mm
Weight	0.523 Kg
Features	
Ingress Protection Rating	IP20
Ambient Temperature Storage	-60 to +70°C
Ambient Temperature Operating	-40 to +70°C
Maximum rated operational voltage	600V
Maximum contactor size	D65
Setting range	23 to 32 A
Terminal capacity flexible cable with ferrule	35mm ²
Tightening torque	9 Nm
Tripping Threshold	1.14 ±0.06 I _n
Auxilliary Contact	
Thermal amperage	5A
Tightening torque	1.85 Nm
Terminal capacity flexible cable with ferrule	2.5mm ²

ⓘ ALL PRODUCTS, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE.

Information provided in data sheets and/or specifications may vary from actual results in different applications and performance may vary over time. **All products must be installed according to manufacturers instructions.**

Europa House, Airport Way, Luton, Beds, LU2 9NH Tel: 01582 692 440 / Fax: 01582 692 450 e-mail: sales@europacomponents.com
 website: <http://www.europacomponents.com>