

Electronic housing - EH 45 FLAT DEV-KIT KMGY - 2202529

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




DEV-KIT EH 45 FLAT: contains 1 x EH 45 FLAT housing and PCB terminal blocks (MKDS ... 5,08), supplied in individual parts

Why buy this product

- ✓ Flat housing with overall width of 45 mm
- ✓ PCB terminal blocks with 5.08 mm pitch, conductor cross section 2.5 mm²
- ✓ Optional hole matrix PCB for soldering THT components by hand

Key Commercial Data

Packing unit	1 pc
GTIN	 4 055626 141794
Weight per Piece (excluding packing)	81.6 g
Custom tariff number	85369010
Country of origin	Germany
Product key	ACHIEA

Technical data

General

Housing type	Component housing
Housing material	ABS
Color	light gray

Ambient conditions

Ambient temperature (operation)	-40 °C ... 80 °C (depending on power dissipation)
---------------------------------	---

Dimensions

Length	75.4 mm
Constructional height	53.5 mm
Width	45 mm

Technical data

Flammability rating according to UL 94	HB
--	----

Electronic housing - EH 45 FLAT DEV-KIT KMGY - 2202529

Classifications

eCl@ss

eCl@ss 4.0	27180401
eCl@ss 4.1	27180401
eCl@ss 5.0	27180506
eCl@ss 5.1	27180506

ETIM

ETIM 3.0	EC001031
ETIM 4.0	EC001031
ETIM 5.0	EC001031

UNSPSC

UNSPSC 6.01	31261501
UNSPSC 7.0901	31261501
UNSPSC 11	31261501
UNSPSC 12.01	31261501
UNSPSC 13.2	31261501

Accessories

Accessories

Electronic housing - EH SNAPLOCK SET WALL MOUNT OG - 2202007

Component housing, Color: orange



Additional products

PCB - EH 45F/16 DEV-PCB - 2202552

Perforated grid board for the EH 40 FLAT DEV-KIT; for MKDS-5,08 terminal blocks; ideal for manual soldering

