

Electronic housing - UM-BASIC 108 100MM DEV-KIT KMG - 2202528

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)


DEV-KIT UM-BASIC: contains 1 x UM-BASIC 100MM profile housing and PCB terminal blocks (SMKDS), supplied in individual parts



Why buy this product

- ✓ Profile housing with overall width of 104 mm
- ✓ PCB terminal blocks with 5.08 mm pitch, conductor cross section 2.5 mm²
- ✓ Optional hole matrix PCB for soldering THT components by hand

Key Commercial Data

Packing unit	1 pc
GTIN	 4 055626 141787
Weight per Piece (excluding packing)	184.4 g
Custom tariff number	85369010
Country of origin	Germany
Product key	ACHIFA

Technical data

General

Housing type	Component housing
Housing material	PVC / PA
Color	light gray

Ambient conditions

Ambient temperature (operation)	-15 °C ... 50 °C (depending on power dissipation)
---------------------------------	---

Dimensions

Length	127.8 mm
Constructional height	40 mm
Width	120 mm

Technical data

Flammability rating according to UL 94	V0
--	----

Electronic housing - UM-BASIC 108 100MM DEV-KIT KMG - 2202528

Classifications

eCl@ss

eCl@ss 4.0	27180401
eCl@ss 4.1	27180401
eCl@ss 5.0	27180506
eCl@ss 5.1	27180506

ETIM

ETIM 3.0	EC001031
ETIM 4.0	EC001031
ETIM 5.0	EC002779

UNSPSC

UNSPSC 6.01	31261501
UNSPSC 7.0901	31261501
UNSPSC 11	31261501
UNSPSC 12.01	31261501
UNSPSC 13.2	31261501

Accessories

Additional products

PCB - UM-BASIC 108/32 DEV-PCB - 2202551



Perforated grid board for the UM-BASIC 108 DEV-KIT; for SMKDS-terminal blocks; ideal for manual soldering