

**SOLID ABS 2819 13 G**



Sample photo

**Order symbol:** ABS 2819 13 G  
**Product nbr:** 5880360  
**Description:** Enclosure, ABS  
**Remarks:** Grey cover

**EAN:** 6418074039026  
**EI. number:**  
 Finland: 3423755  
 Electric No. Italy: 7410120  
 Electric No. Sweden: 2539709

Including: Base with screws for mounting plate, cover with PUR gasket and polyamide cover screws.

**Dimensions: Length Width Height Accessories:**

Dimensions:	Length	Width	Height	Accessories:
mm:	278	188	130	EKJXT Mounting plate isolated
inch:	10.9	7.4	5.1	EKV 12 DIN-35 Mounting rail
				EKV 22 DIN-35 Mounting rail
				EKJZR Extension frame

**Materials:**

<b>Material:</b>	ABS
<b>Base colour:</b>	RAL 7035 -light grey
<b>Cover screws material:</b>	Polyamide
<b>Cover colour:</b>	RAL 7035 -light grey
<b>Cover screws colour:</b>	Grey
<b>Gasket material:</b>	Polyurethane

**Rating:**

Ingress Protection (EN 60529):	IP66/IP67
Impact Resistance (EN 62262):	IK08
Electrical insulation:	Totally insulated
Halogen free (DIN/VDE 0472, Part 815):	1
Flammability Rating:	UL 94 HB
Glow Wire Test (IEC 695-2-1) °C:	650
NEMA Class:	NEMA 1, 4, 4X, 6, 12, 13

**Temperatures:**

<b>Temperature °C (short term):</b>	-40 ... 80 °C
<b>Temperature °C (continuous):</b>	-40 ... 60 °C
<b>Temperature °F (short term):</b>	-40 ... 175 °F
<b>Temperature °F (continuous):</b>	-40 ... 140 °F

**Certificates:**

SGS Fimko

**Accessories:**

EKJVT	Mounting plate
-------	----------------

