

SOLID ABS 2828 13 G



Sample photo

Order symbol: ABS 2828 13 G
Product nbr: 5880362
Description: Enclosure, ABS
Remarks: Grey cover

EAN: 6418074039064
EI. number:
 Finland: 3423763
 Electric No. Italy: 7410140
 Electric No. Sweden: 2539717

Including: Base with screws for mounting plate, cover with PUR gasket and polyamide cover screws.

Dimensions:	Length	Width	Height	Accessories:	
mm:	278	278	130	EKOXT	Mounting plate isolated
inch:	10.9	10.9	5.1	EKV 22	DIN-35 Mounting rail
				EKOZR	Extension frame

Materials:	
Material:	ABS
Base colour:	RAL 7035 -light grey
Cover screws material:	Polyamide
Cover colour:	RAL 7035 -light grey
Cover screws colour:	Grey
Gasket material:	Polyurethane

Rating:
Ingress Protection (EN 60529): IP66/IP67
Impact Resistance (EN 62262): IK08
Electrical insulation: Totally insulated
Halogen free (DIN/VDE 0472, Part 815): 1
Flammability Rating: UL 94 HB
Glow Wire Test (IEC 695-2-1) °C: 650
NEMA Class: NEMA 1, 4, 4X, 6, 12, 13

Temperatures:	
Temperature °C (short term):	-40 ... 80 °C
Temperature °C (continuous):	-40 ... 60 °C
Temperature °F (short term):	-40 ... 175 °F
Temperature °F (continuous):	-40 ... 140 °F

Certificates:
SGS Fimko

Accessories:	
EKOVT	Mounting plate

