

SOLID ABS 3828 13 G



Sample photo

Order symbol: ABS 3828 13 G
Product nbr: 5880363
Description: Enclosure, ABS
Remarks: Grey cover

EAN: 6418074039088
EI. number:
 Finland: 3423767
 Electric No. Italy: 7410150
 Electric No. Sweden: 2539721

Including: Base with screws for mounting plate, cover with PUR gasket and polyamide cover screws.

Dimensions:			Accessories:	
Length	Width	Height		
mm:	378	278	EKPXT	Mounting plate isolated
inch:	14.9	10.9	EKV 22	DIN-35 Mounting rail
			EKV 32	DIN-35 Mounting rail
			EKPZR	Extension frame
Materials:			Rating:	
Material:	ABS		Ingress Protection (EN 60529): IP66/IP67	
Base colour:	RAL 7035 -light grey		Impact Resistance (EN 62262): IK08	
Cover screws material:	Polyamide		Electrical insulation: Totally insulated	
Cover colour:	RAL 7035 -light grey		Halogen free (DIN/VDE 0472, Part 815): 1	
Cover screws colour:	Grey		Flammability Rating: UL 94 HB	
Gasket material:	Polyurethane		Glow Wire Test (IEC 695-2-1) °C: 650	
			NEMA Class: NEMA 1, 4, 4X, 6, 12, 13	
Temperatures:			Certificates:	
Temperature °C (short term):	-40 ... 80 °C		SGS Fimko	
Temperature °C (continuous):	-40 ... 60 °C			
Temperature °F (short term):	-40 ... 175 °F			
Temperature °F (continuous):	-40 ... 140 °F			
Accessories:				
EKPVT	Mounting plate			

