

ARCA 203015

FIBOX
Enclosing innovations



Sample image

Order symbol: ARCA 203015

Product nbr: 8120020

Description: Cabinet. PC


Remarks: Grey cover. 1-point locking. hinges on the short side

Including: Cabinet base. door with PUR gasket. mounting plate. screws for mounting plate. 3mm double bit lock(s) with key. 5 versions with swinghandle 2-point locking system. Door guide included.

EAN: 6418074079312

El. number:

- Finland: 3423117
- Denmark: 8212091184
- Sweden: 2500109



Dimensions:

	Height	Width	Depth
mm:	200	300	150
inch:	7.87	11.81	6.22

Materials:

Material:	Polycarbonate
Base colour:	RAL 7035 -light grey
Cover colour:	RAL 7035 -light grey
Gasket material:	Polyurethane

Temperatures:

Temperature °C (short term):	-40 ... 120
Temperature °C (continuous):	-40 ... 80
Temperature °F (short term):	-40 ... 250
Temperature °F (continuous):	-40 ... 175

Accessories:

MPMP ARCA 3020	Mounting plate multiperforated (250x150x2 mm - \varnothing 3.6 mm) (250 x 150 x 2)
IDS ARCA 2030	Inner door set (185 x 285 x 35)
MPP ARCA 2030	Mounting plate perforated (250x150x2 mm - 26x11 mm) (150 x 250 x 2)
SBK ARCA 20	Support bar kit (140 x 40 x 30)
MPS ARCA 3020	Mounting plate (250x150x2 mm) (250 x 150 x 2)
SBK ARCA 30	Support bar kit (235 x 40 x 30)
DRS ARCA 203015	DIN rail frame set (285 x 185 x 35)
RCS ARCA 2030	Rain canopy set for size 2030 (20 x 300 x 30)
PMK ARCA 30	PoleMounting kit. for pole \varnothing 100-300mm (385 x 285 x 35)
MPX ARCA 3020	Mounting plate (250x150 mm) (250 x 150 x 5)

Rating:

Ingress protection (EN 60529):	IP66;
Impact Resistance (EN 62262):	IK10;
Electrical insulation:	Totally insulated
Halogen free (DIN/VDE 0472, Part 815):	1
UV resistance:	UL 508
Flammability Rating:	UL 94 5VA
Glow Wire Test (IEC 695-2-1) °C:	960 °C
NEMA Class	NEMA 1, 4, 4X, 12 and 13

Certificates:

Certificate FI 40467